

## VZ Chiller series

Water cooled inverter chiller




# The highest peak in chiller technology

## EWWD-VZ chiller series

An increasing demand for high efficient HVAC systems drives our product development mission.

By answering market demands and offering new opportunities we anticipate on the future HVAC market needs.







### 7.9

## Top efficiency ESEER

The EWWD-VZ chiller series were developed and manufactured to answer the growing market demands on high efficient chiller series.

Thanks to the continuous evolution in components' technology, we are the first to reach the highest peak in chiller efficiency and technology.





## Single compressor

450 kW - 1,053 kW

Full inverter water cooled chiller






Highest efficiency in the market in its category





## Dual compressor & dual circuit unit



- › 2 of everything:
- 2 compressors,
- 2 expansion valves,
- 2 condensers,...

SERIES



New condenser design with integral oil separator

High efficient flooded heat exchangers

Unique Daikin single screw compressor technology



## Why choose EWWD-VZ chiller series?


1 Top class efficiency: ESEER up to 8.5 – EER up to 5.8

#### New generation Daikin inverter single screw compressors

Importance of ESEER:


Power consumption significantly reduced at part loads where the machine will run for 97% of the operation hours (Eurovent load profile)






#### Why choose an inverter chiller?

- > -25% energy consumption
- > -25% CO<sub>2</sub> emissions
- > -25% running costs
- > Return on investment < 2 years vs non-inverter chiller



#### Why are we better than others?

- > Full inverter capacity control down to 20%
- > No inefficient mechanical unloading slides



#### New generation high efficiency heat exchangers

> Flooded type technology allowing maximizing unit performances

> Latest technology enhanced surface tubes

#### **Evaporator tubes:**

- > Outside: Cavities for optimized nucleate boiling
- > Inside: Helical structure

#### Condenser tubes:

- > Outside: Optimized for condensation
- > Inside: Helical structure









#### Optimized design

#### Pressure drops reduced by half

- > meaning 1°C lower condensing temperature
- > + 3.5 % efficiency





Did you know that you can maximize your BREEAM and programme score and LEED green building programme score with the Daikin HVAC solutions?

## 2 Compact unit





40 % footprint reduction in comparison to traditional water cooled series thanks to:


#### 1. New single pass condenser technology

- . High heat exchange performances thanks to couterflow design
- . Low water pressure drops < 30 kPa


#### 2. New integrated oil separator technology

- . Low oil carry over
- . Low refrigerant pressure drops






## 3 Application flexibility



## 4 Connectivity

#### Remote access with one click

- > Remote monitoring
- > System optimization
- > Preventive maintenance



## 5 Future readiness: Choose for today's best solution and be ready for the future!

## R-134A refrigerant, still today the best possible choice:

- > Still most efficient refrigerant.
- Availability in high quantitates and at competitive prices.
- > No phase out planned in F-GAS regulation.
- > Classified as non flammable

#### All VZ units are 'new refrigerant ready'!

Possibility to retrofit them in the future with lower GWP refrigerants (HFO blends).

## Supporting tools

#### Product video








#### Marketing material

All marketing material and tools for the EWWD-VZ range can be downloaded from the business portal.

Asset finder > Campaign > VZ chiller series







#### Web

Want to know more about this product?
Have a look at our dedicated webpage:
www.daikineurope.com/vzchillerseries

## Technical specifications - single compressor range

#### Standard efficiency, standard sound

Cooling only /Hea	ting only				EWWD600VZSSA1	EWWD700VZSSA1	EWWD760VZSSA1	EWWD890VZSSA1	EWWDC10VZSS	
Cooling capacity	Nom.			kW	610	704	757	894	1,039	
Heating capacity	Nom.			kW	756.7	877.8	943.2	1,107	1,292	
Power input	Cooling	Nom.		kW	110	132	142	162	196	
	Heating	Nom.		kW	140	166	179	201	244	
EER					5.51	5.31	5.31	5.52	5.28	
ESEER					7.25	7.30	7.40	7.27	7.52	
COP					5.42	5.27	5.28	5.5	5.3	
Dimensions	Unit	Height		mm	2,120	2,120	2,120	2,290	2,480	
		Width		mm	1,180	1,180	1,180	1,240	1,340	
		Depth		mm	3,460	3,460	3,460	3,690	3,690	
Weight	Unit	•		kg	2,892	2,928	2,941	3,451	4,237	
_	Operation weigh	nt		kg	2,977	3,033	3,053	3,611	4,488	
Water heat	Туре					Floode	ed single pass shell ar	nd tube	·	
exchanger -	Water volume			I	88	88	96	134	156	
evaporator	Water flow rate	Cooling	Nom.	l/s	29.3	33.8	36.3	42.9	49.9	
		Heating	Nom.	I/s	29.6	34.2	36.7	43.5	50.4	
	Water pressure drop	Cooling	Nom.	kPa	80.0	106.0	89.0	98.0	104	
		Heating	Nom.	kPa	82	108	90	100	106	
Water heat	Type					Sii	ngle pass shell and tu	be		
exchanger -	Water volume			I	81	102	102	126	217	
condenser	Water flow rate	Cooling	Nom.	l/s	34.5	40.2	43.1	50.7	59.4	
		Heating	Nom.	l/s	36.46	42.33	45.47	53.38	62.35	
	Water pressure drop	Cooling	Nom.	kPa	54.0	41.0	46.0	44.0	33.0	
		Heating	Nom.	kPa	60	44	51	48	36	
Compressor	Туре					Inverter o	driven single screw co	mpressor		
	Quantity				1					
Sound power level	Cooling	Nom.		dBA	101	105	105	105	108	
Sound pressure level	Cooling	Nom.		dBA	82	86	86	86	89	
Operation range	Evaporator	Cooling	Min.~Max.	°CDB			-3~20			
	Condenser	Cooling	Min.~Max.	°CDB			16~63			
Refrigerant	Type / GWP / Circ	cuits			R-134a / 1,430 / 1					
Refrigerant charge	Per circuit			kg	100	110	110	170	180	
				TCO₂eq	143	157	157	243	257	
Piping connections	Evaporator wate	r inlet/out	let (OD)		141.3	141.3	141.3	168.3	219.1	
	Condenser water	r inlet/outl	et (OD)		168.3	168.3	168.3	219.1	219.1	
Unit	Starting current	Max.		Α	179	214	245	295	344	
	Running current	Cooling	Nom.	Α	171	202	220	249	300	
		Max.	Α	Α	256	306	350	421	491	
Power supply	Phase/Frequency	y/Voltage		Hz/V			3~/50/400			

#### High efficiency, standard sound


Cooling only/Heat	ing only		EWW	D-VZXS	450	500	610	710	800	900	C11
Cooling capacity	Nom.			kW	449	501	613	713	793	901	1,053
Heating capacity	Nom.			kW	553	617.2	756.7	882.2	984.6	1,110	1,302
Power input	Cooling	Nom.		kW	81.1	89.6	108	128	146	158	192
	Heating	Nom.		kW	102	112	138	163	185	199	240
EER					5.53	5.58	5.64	5.54	5.43	5.67	5.46
ESEER					7.51	7.92	8.10	8.20	8.22	7.92	8.17
COP					5.45	5.49	5.48	5.42	5.33	5.58	5.43
Dimensions	Unit	Height		mm	2,090	2,	120	2,230	2,290	2,	480
		Width		mm		1,180		1,220	1,240	1,3	340
		Depth		mm	3,460			3,690		3,830	
Weight	Unit			kg	2,968	2,911	3,102	3,470	3,451	4,257	4,552
•	Operation weigh	nt		kg	3,098	3,006	3,274	3,648	3,611	4,518	4,860
Water heat	Type						· · · · · · · · · · · · · · · · · · ·	single pass she	· · ·		, , , , , ,
exchanger -	Water volume			- 1	70	88	136		34	168	199
evaporator	Water flow rate	Cooling	Nom.	l/s	21.6	24.0	29.4	34.2	38.0	43.2	50.4
		Heating	Nom.	l/s	21.7	24.2	29.7	34.5	38.4	43.7	50.9
	Water press. drop	Cooling	Nom.	kPa	89.0	63.0	59.0	63.0	55.0	67.0	58.0
		Heating	Nom.	kPa	90	64	60	64	56	68	59
Water heat	Type						Sinal	e pass shell and	d tube	'	
exchanger -	Water volume			T I	81	92	126	145	126	217	241
condenser	Water flow rate	Cooling	Nom.	l/s	25.4	28.3	34.7	40.4	45.2	50.9	59.9
		Heating	Nom.	I/s	26.68	29.78	36.53	42.60	47.53	53.59	62.85
	Water press. drop	Cooling	Nom.	kPa	31.0	28.0	22.0	20.0	24.0	25.0	25.0
		Heating	Nom.	kPa	34	31	24	22	27	28	27
Compressor	Туре				-		Inverter driv	en single screv	v compressor	-	
	Quantity							1			
Sound power level		Nom.		dBA	97	99	101		105		108
Sound pressure level		Nom.		dBA	78	80	82		86		89
Operation range	Evaporator	Cooling	Min.~Max	°CDB				-3~20			
operation range	Condenser	Cooling	Min.~Max.	°CDB				16~65			
Refrigerant	Type / GWP / Circ							R-134a / 1,430 /	1		
Refrigerant charge				kg	(	95	100	110	7	70	180
. ggc				TCO₂eq		36	143	157		43	257
Piping connections	Evaporator wate	r inlet/out	let	mm		141.3			8.3		19.1
, 3	Condenser water			mm	16	68.3			219.1		
Unit	Starting current			А	155	173	179	214	256	295	344
-	Running current		Nom.	A	126	140	171	201	229	249	299
	g carrent	Max		A	222	247	256	306	366	421	491
Power supply	Phase/Frequency			Hz/V		217	230	3~/50/400	300	121	171

#### Premium efficiency, standard sound

Cooling only/Heat	ting only		EWW	D-VZPS	505	715	910		
Cooling capacity	Nom.			kW	505	718	908		
Heating capacity	Nom.			kW	619.7	885.3	1,115		
Power input	Cooling	Nom.		kW	87.5	126	156		
	Heating	Nom.		kW	110	161	196		
EER					5.77	5.66	5.81		
ESEER					8.15	8.48	8.25		
COP					5.62	5.49	5.68		
Dimensions	Unit	Height		mm	2,090	2,430	2,480		
		Width		mm	1,180	1,330	1,340		
		Depth		mm		3,690	3,830		
Weight	Unit	·		kg	3,247	4,082	4,346		
3	Operation weigh	nt		kg	3,375	4,349	4,660		
Water heat	Type				Flooded single pass shell and tube				
exchanger -	Water volume			- 1	96	168	199		
evaporator	Water flow rate	Cooling.	Nom.	l/s	24.2	34.4	43.5		
·		Heating	Nom.	l/s	24.4	34.7	44		
	Water press. drop	Cooling	Nom	kPa	55.0	42.0	44.0		
		Heating	Nom.	kPa	56	43	45		
Water heat	Туре				Single pass shell and tube				
exchanger -	Water volume			- 1	126	217	241		
condenser	Water flow rate	Cooling	Nom.	l/s	28.5	40.6	51.2		
		Heating	Nom.	l/s	29.93	42.7	53.83		
	Water press. drop	Cooling	Nom.	kPa	15	17	19		
		Heating	Nom	kPa	17	18	21		
Compressor	Туре				Inverter driven single screw compressor				
	Quantity					1			
Sound power level	Cooling	Nom.		dBA	99	105			
Sound pressure level	Cooling	Nom.		dBA	80	86			
Operation range	Evaporator	Cooling	Min.~Max.	°CDB	-3~20				
	Condenser	Cooling	Min.~Max.	°CDB	16~65				
Refrigerant	Type / GWP / Cire	cuits			R-134a / 1,430 / 1				
Refrigerant charge	Per circuit			kg	100	150	180		
				TCO₂eq	143	215	257		
Piping connections Evaporator water inlet/outlet mm				mm	141.3	219.1			
			mm		219.1				
Unit	Starting current	Max		Α	173	214	295		
	Running current	Cooling	Nom.	Α	138	200	247		
		Max		Α	247	306	421		
Power supply	Phase/Frequenc	v/Voltage		Hz/V		3~/50/400			



**Daikin Europe N.V.** Naamloze Vennootschap Zandvoordestraat 300 · 8400 Oostende · Belgium · www.daikin.eu · BE 0412 120 336 · RPR Oostende (Responsible Editor)





EN17-418







Daikin Europe N.V. participates in the Eurovent Certification programme for Liquid Chilling Packages (LCP), Air handling units (AHU) and Fan coil units (FCU), Check ongoing validity of certificate online: www.eurovent-certification.com or using: www.certifiash.com

The present publication is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this publication to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from

Printed on non-chlorinated paper. Prepared by La Movida